

Light Motion Suite

- wireless full-body tracking -

1. Technical Characteristics

Light motion suit is the set of inertial measurement units (IMU), nodes. A node may perform function of a gate that is to be connected to USB, via its 5-pin connector. Each node may be connected up to 3 other nodes via 4-pin connectors. Maximum number of nodes connected to a gate is 10 (including internal node).



We offer to customers either separate IMUs or wireless full-body tracking set that consist of:

- Wearable PC, including:
 - o IMU compartment
 - Internal battery
 - o Wi-Fi router
 - Ubuntu Linus OS
- 15 IMUs
- Straps and cables





Lux Prototyping S.A.R.L. 23, rue des Bateliers, 6713 Grevenmacher Luxembourg

Fax: +352-26714534 Email: info@trivisio.com Web: www.trivisio.com

+352-26714533

Page 1 of 2

Tel:




Light Motion Suite

- wireless full-body tracking -

2. Software:

For separate IMUs Colibri API may be used. It's a cross-platform library for Windows, Mac OS X and Linux for configuring IMUs and acquiring data. It includes GUI for easy configuring:



For wireless set VRPN may be used. It's open source client/server software for transferring sensor data via network. Often motion capture software has a VRPN plug-in. VRPN server runs in the wearable PC. You must have VRPN client to get date. Run server from client PC: suit_config –c <configuration file> -f <frequency>

vrpn orientation Colibri@192.168.8.1

Wireless set may be used also in data-logger mode, saving captured data to flash memory.

3. Technical Specifications

suit run

Sensor type:	3-DOF orientation, based on inertial and magnetic field sensors
Gyroscope:	Scale: ±2000 °/s
Accelerometer:	Scale: ±16 g
Magnetic field sensor	May be disabled for industrial environments
Orientation accuracy	Pitch/Roll: 1° Yaw: 2°
Working frequency	260 Hz with 15 nodes (every node runs at this freq.), 500 Hz with only 1 node
Dimensions (W/H/D)	
Sensor	30 mm x 10 mm x 30 mm
Wearable-PC	TBD
Connection type	USB (separate IMUs) / Wi-Fi (wireless set)
Latency	2 ms /5 ms
Power consumption	0.15 W / 4 W (3-hours operation with internal battery

Subject to technical modifications



Lux Prototyping S.A.R.L. 23, rue des Bateliers, 6713 Grevenmacher Luxembourg Tel: +352-26714533
Fax: +352-26714534
Email: info@trivisio.com
Web: www.trivisio.com

2018-07-11 Page 2 of 2